


Passive Components &gt; Resistors &gt; Surface Mount Resistors &gt; Thick Film Resistor: Current Sense

Resistor Type: **Current Sensing Resistor**Element Type: **Thick Film**Package Size Code: **2512**Power Rating: **2 W**Resistance Value: **.068  $\Omega$** [All Thick Film Resistor: Current Sense \(142\)](#)

## Features

### Product Type Features

Resistor Type	Current Sensing Resistor
Element Type	Thick Film
Package Size Code	2512

### Configuration Features

Number of Resistors	1
---------------------	---

### Electrical Characteristics

Power Rating	2 W
Resistance Value	.068 $\Omega$
Resistance Class	Up to 1k $\Omega$
Passive Component Tolerance	5 %

### Termination Features

Surface Mount Resistor Termination Type	Solder
---	--------

Number of Terminations	2
------------------------	---

### Dimensions

Product Height	.74 mm [.029 in]
Product Length	6.35 mm [.25 in]
Product Width	3.15 mm [.124 in]

### Usage Conditions

Temperature Coefficient	$\pm 300$ ppm/ $^{\circ}\text{C}$
-------------------------	-----------------------------------

### Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

### Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Not Compliant

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-C339-R529A  
Thick Film Resistor: Current Sense



TE Part # 2176050-8  
RLP73N 1E R10 5% 5K RL

## Also in the Series | CGS RLP73



Surface Mount Resistors(337)

## Customers Also Bought



TE Part #1-2176057-6  
RLP73M 3A R043 1% 1K RL



TE Part #2-1879011-7  
SMF2 2K7 5%



TE Part #1-1393243-8  
RTE24730



TE Part #1367147-1  
SFP COVER, UNPLATED



TE Part #360042-1  
250 FASTON HSG.,TAB,NATURAL



TE Part #2176399-5  
3502 560R 5%



TE Part #1-1825059-8  
ADF04STTR04=DIP S,FLUSH,SMT-GW



TE Part #1-1622459-0  
LR1 1% 3K09



## Documents

### Product Drawings

#### RLP73N 3A R068 5% 2K RL

English

---

### CAD Files

#### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2-2176058-1\\_BA.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-2176058-1\\_BA.3d\\_jgs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-2176058-1\\_BA.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

#### SMD Low Ohmic Current Sense Resistors - Type RL73 Series

English