

ROX3SJ150K

✓ ACTIVE

Neohm | Neohm ROX

TE Internal #: 1-1625892-4

Through-Hole Power Resistor, Metal Oxide Film, 3 W, 150K ohm, 5 %, ±350 ppm/°C, Axial-Leaded, Copper Termination, 16 x 5.5 mm, Ammo Packed, Neohm ROX

[View on TE.com >](#)



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**

Element Type: **Metal Oxide Film**

Power Rating: **3 W**

Resistance Class: **1kΩ – 1MΩ**

Resistance Value: **150K Ω**

Features

Usage Conditions

Operating Temperature Range	-55 – 235 °C
Temperature Coefficient	±350 ppm/°C

Electrical Characteristics

Operating Voltage	350 V
Power Rating	3 W
Resistance Class	1kΩ – 1MΩ
Resistance Value	150K Ω
Passive Component Tolerance	5 %

Product Type Features

Resistor Type	Power Resistor
Element Type	Metal Oxide Film

Configuration Features

Number of Resistors	1
---------------------	---

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2



Dimensions

Passive Component Dimensions	16 x 5.5 mm
------------------------------	-------------

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

ROX3SJ150K

Through-Hole Power Resistor, Metal Oxide Film, 3 W, 150K ohm, 5 %, ±350 ppm/°C, Axial-Leaded, Copper Termination, 16 x 5.5 mm, Ammo Packed, Neohm ROX





TE Part # 1625881-2
1W STD M/OX 2% 220R



TE Part # 2-1625892-1
3W SM M/OX 5% 1K0



TE Part # 6-1676123-7
1/2W SM M/OX 5% 470R



TE Part # 1625893-5
5W SM M/OX 5% 47K



TE Part # 4-1625886-1
1W SM M/OX 5% 820K

Also in the Series | Neohm ROX



Through-Hole Resistors(783)


Customers Also Bought



TE Part #66098-9
III+ PIN, 18-16, 30AU/FL, STRIP




TE Part #532434-8
HDI RECP ASSY 4 ROW 220 POS




TE Part #1-1625867-1
RP 1J 0.166W 22K1 0.1% 25PPM 1K RL




TE Part #1625893-6
5W SM M/OX 5% 150K



TE Part #2-2176370-6
RQ 0603 787R 0.1% 10PPM 5K RL



TE Part #92007-1
CMPSNP CONT. METINTERCONN SYS.



TE Part #92009-2
RCPT HSG, METRIC INTERCONN SYS



TE Part #10217784-00
ABD, AD-101, COMPACT ASSY, 4MM



TE Part #177537-3
2.5 M.I.S POST HDR ASSY 3P



TE Part #174056-4
040 MLC PLUG HSG 2P GREEN

Documents

Product Drawings

3W SM M/OX 5% 150K

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1625892-4_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1625892-4_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1625892-4_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

Flame Proof Power Metal Oxide Film Resistors - Type ROX Series - Tyco Electronics Passives

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English