



Pushing Performance
Since 1945

har-port USB 3.0 A-A; PFT



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 452 1902
Specification	har-port USB 3.0 A-A; PFT
HARTING eCatalogue	https://b2b.harting.com/09454521902

Identification

Category	Connectors
Series	har-port
Element	Service interfaces
Specification	USB 3.0

Version

Connection type	Type A jack - type A jack
Fixing	Screwable in cover plates

Technical characteristics

Ambient temperature	-25 ... +70 °C
Mating cycles	≥1,500
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	silver
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene

Specifications and approvals

Specifications	EN 45545-2
UL / CSA	UL 1863 DUXR2.E470046
	CSA-C22.2 No. 182.4, No. 233-09 DUXR8.E470046
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	1.5 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140060470
ETIM	EC002599
eCl@ss	27060304 Appliance cord (data cable)