



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**  
Connector & Housing Type: **Receptacle**  
Number of Positions: **1**  
Terminal Orientation: **Straight**  
Primary Product Color: **Black**

Features

Dimensions

Product Length	18 mm[.71 in]
----------------	---------------

Packaging Features

Packaging Quantity	1000
--------------------	------

Product Type Features

Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	Without



Mechanical Attachment

Mating Alignment	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT
------------------	-----

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 626064-5  
ISOLADOR

TE Part # 925015-1  
FF 110 REC HSG 3P NYLON BLACK

TE Part # 1982857-1  
FASTON HOUSING

TE Part # 626062  
FASTIN-ON HOUSING REC PA66 NATURAL

TE Part # 926728-1  
FF 110 REC HSG 4P NYLON BLACK

TE Part # 176987-2  
FF 250 PLUG HSG 1P NYLON BLACK

TE Part # 1-172131-1  
FF 250 CAP HSG 3P NYLON NAT

TE Part # 140885-5  
FF 250 REC HSG 6P NYLON BLACK

TE Part # 173271-2  
250 SERIES HORN CONNECTOR, PLUG HSG

TE Part # 968864-1  
FF 110 REC HSG 2P NYLON NAT

Also in the Series | FASTON 187

Crimp Terminal Housings(41)

Insertion & Extraction Tools(1)

Joints & Splices(1)

PCB Terminals(42)

Quick Disconnects(207)

Splices(1)

Customers Also Bought





TE Part #883745-000  
[TXR40AB00-1618AI](#)

  
Single Wall

TE Part #F83512-000  
[82A0813-10-9](#)



TE Part #YDTS24F17-06JNV001  
[RECP ASSY](#)




TE Part #YDTS26W17-08BNV001  
[PLUG ASSY](#)



TE Part #1982857-1  
[FASTON HOUSING](#)



TE Part #CA0866-000  
[TXR54AB00-2807AI](#)




TE Part #485111-000  
[TXR54AB90-2410AI](#)



TE Part #AAA8329-00  
[91D1-12-09-1-ZBC-HE200](#)



TE Part #YDTS26W13-04PBC001  
[PLUG ASSY](#)



TE Part #D69957-000  
[D-500-0467-1-612-240](#)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1982859-1\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1982859-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1982859-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English