




Connectors > Pluggable IO Connectors & Cages > OSFP Cage Assembly: EMI Springs



Form Factor: **OSFP**

Pluggable I/O Product Type: **Cage Assembly**

Sealable: **No**

Operating Temperature Range: **-55 – 85 °C [-67 – 185 °F]**

Number of Positions: **60**

[All OSFP Cage Assembly: EMI Springs \(11\)](#)

Features

Mechanical Attachment

PCB Mounting Style	Through Hole - Press-Fit
--------------------	--------------------------

Product Type Features

Cage Type	Single
Form Factor	OSFP
Pluggable I/O Product Type	Cage Assembly
Sealable	No

Configuration Features

Number of Positions	60
Number of Ports	1
Port Matrix Configuration	1 x 1

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Other

--	--



Included Lightpipe	No
EMI Containment Feature Type	Internal/External EMI Springs
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2821906-5
OSFP - OSFP, 1 METER, 30AWG



TE Part # 2335033-3
OSFP - 2 QSFP, 3 METER, 26AWG



TE Part # 2324441-2
OSFP - 2 QSFP, 1.0 METER, 30AWG



TE Part # 2336063-3
OSFP - 4 QSFP, 3 METER, 26AWG



TE Part # 2317857-2
DUST AND EMI PLUG, PLATED, OSFP



TE Part # 2324442-2
OSFP - 4 QSFP, 1 METER, 30AWG



TE Part # 2821906-7
OSFP - OSFP, 2 METER, 30AWG



TE Part # 2324698-1
DUST PLUG, OSFP



TE Part # 2336065-3
OSFP - OSFP, 3 METER, 26AWG



TE Part # 2336064-3
OSFP - 8 SFP, 3 METER, 26 AWG



TE Part # 2324441-4
OSFP - 2 QSFP, 2 METER, 30AWG



TE Part # 2324443-4
OSFP - 8 SFP, 2 METER, 30AWG



TE Part # 2324443-2
OSFP - 8 SFP, 1 METER, 30AWG



TE Part # 2324442-4
OSFP - 4 QSFP, 2 METER, 30AWG




TE Part # CAT-P65-N49
OSFP Connector Assembly: Surface Mount

Customers Also Bought



TE Part #5352069-1
Z-PACK/B25 RAF 125P



TE Part #1658391-2
SFP CAGE&PT ASSY PRESS FIT 2X1




TE Part #2170903-1
RECEPTACLE HM-EZD+, 4PAIRS 10COLUMNS




TE Part #3-1827253-6
.5FHP05H,220,S,GIG,08/Sn,HT,NSYes




TE Part #2007181-1
SFP+ 1x2 Cage Assy, EMI Gasket



TE Part #1761014-3
SFP 1X2 CAGE ASSY, PRESS FIT



TE Part #2274845-1
CFP2 RECEPTACLE ASSEMBLY



TE Part #2342934-3
QSFP-DD 1X1, STANDARD, W/ ZIPPER HS



TE Part #2057417-1
IMP100S,R,RA4P8C,UG,39



TE Part #2335809-1
CAGE ASSEMBLY WIHT SPRING,SFP-DD 1X1

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2317416-1_B6.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2317416-1_B6.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2317416-1_B6.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

OSFP Cages, Connectors, and Cable Assemblies (English)

English

Product Specifications

Application Specification

English