

Stamped contacts Crimp female contacts diameter 1,6 mm for wire gauge AWG 20 - 16 gold plated

Part No. HN02 016 0002 2

Series Contacts

Subseries Contact Stamped contacts

COMMON CHARACTERISTICS		
Contact diameter		1,6 mm
Insulation diameter		1,8 - 2,8 mm
Wire gauge from		0,5
Wire gauge to		1,5
Wire gauge (AWG) from		20
Wire gauge (AWG) to		16
Packaging / supplied as		Contacts on reel for crimp machines-right hand side
No. of pieces		2.000
Sex of Contact		Socket
Type of contact		Stamped/rolled crimp contact
ELECTRICAL CHARACTERISTICS		
Contact resistance	DIN EN 60512-2-1, Test 2a / IEC 60512-2-1, Test 2a	< 5 mΩ

