

# Series 804 Push-Pull Mighty Mouse Protective Plug Cover 809-198 Ordering Information



**Protect Connectors From Damage**  
Machined aluminum covers prevent ingress of contamination and water.

**Stainless Steel Fittings and Rings**  
Choose small diameter eye fittings for panel attachment. Larger rings fit under the jam nut or over cable jackets. Split rings can be installed on fully assembled cables.

**Polyurethane-Coated SST Wire Rope** offers high strength, excellent abrasion resistance and good flexibility. Or, choose Teflon® jacket for high temperature exposure.

**Braided Nylon Rope** provides excellent flexibility and good abrasion resistance, and can be ordered with slip knot fittings for easy installation on any size cable.

How To Order							
Sample Part Number	809-198	M	9	H	6	-14	A
Series (See Table I)	809-198 = Plug Cover						
Shell Material / Finish	<b>C</b> = Aluminum / Black Anodize (Non-Conductive) RoHS Compliant <b>M</b> = Aluminum / Electroless Nickel RoHS Compliant <b>NF</b> = Aluminum / Cadmium with Olive Drab Chromate <b>ZN</b> = Aluminum / Zinc-Nickel with Olive Drab Chromate <b>ZNU</b> = Aluminum / Zinc-Nickel with Black Chromate <b>MT</b> = Aluminum / Nickel-PTFE RoHS Compliant <b>Z1</b> = Stainless Steel / Passivated RoHS Compliant						
Shell Size	5, 6, 7, 8, 9, 10, 11, 12, 14, 15						
Attachment Type	<b>D</b> = Bead Chain, CRES, Passivate <b>F</b> = Wire Rope, Nylon Jacket <b>G</b> = Nylon Rope <b>H</b> = SST Wire Rope, Fluoropolymer Jacket <b>N</b> = No Attachment <b>R</b> = Wire Rope, PVC Jacket <b>S</b> = SST Sash Chain <b>SK</b> = Nylon Rope With Slip Knot <b>T</b> = SST Wire Rope, No Jacket <b>U</b> = SST Wire Rope, Polyurethane Jacket  "SST" = Stainless Steel						
Attachment Length (inches)	Omit for attachment Type N (No Attachment) Example: "-6" equals six inch length						
Attachment Code (See Table II)	Small Ring = <b>01</b> thru <b>06</b> Large Ring = <b>14</b> thru <b>33</b> Split Ring = <b>50</b> thru <b>68</b>						
Alternate Key Position	Omit for master keyway only, for all other positions indicate <b>A</b> , <b>B</b> , <b>C</b> , <b>D</b> , <b>E</b> , or <b>F</b>						

Table I: Cover Style
<b>809-198</b> Push-Pull Plug Cover

Table II: Attachment Code	
Omit for attachment Type <b>N</b> (No Attachment) and <b>SK</b> (Slip Knot)	
	<b>-01</b> - .126 (3.20) I.D. <b>-02</b> - .145 (3.68) I.D. <b>-04</b> - .188 (4.78) I.D. <b>-06</b> - .197 (5.00) I.D.
<b>Small Ring</b>	
	<b>-32</b> - .265 (6.73) <b>-29</b> - .315 (8.00) <b>-14</b> - .385 (9.78) <b>-33</b> - .510 (12.95) <b>-15</b> - .445 (11.30) <b>-16</b> - .570 (14.48) <b>-17</b> - .635 (16.13) <b>-18</b> - .695 (17.65) <b>-27</b> - .766 (19.46) <b>-26</b> - .950 (24.13) <b>-31</b> - .820 (20.83) <b>-28</b> - 1.015 (25.78) <b>-20</b> - 1.070 (27.18) <b>-21</b> - 1.135 (28.83)
<b>Solid Ring</b>	
	<b>-50</b> - .420 (10.67) I.D. <b>-52</b> - .480 (12.19) I.D. <b>-54</b> - .635 (16.13) I.D. <b>-56</b> - .745 (18.92) I.D. <b>-58</b> - .885 (22.48) I.D. <b>-60</b> - 1.010 (25.65) I.D. <b>-64</b> - 1.125 (28.58) I.D. <b>-68</b> - 1.345 (34.16) I.D.
<b>Split Ring</b>	

Dimensions in Inches (millimeters) are subject to change without notice.