

RP73PF1E1K43BTD

✓ ACTIVE

Holsworthy | Holsworthy RP73

TE Internal #: 1-2176306-0

Surface Mount Precision Resistor, Thin Film, 0402, .1 W, 1.43K ohm, .1 %, ±25 ppm/°C, Solder, 2 Terminations, Height .3 mm [.012 in], Holsworthy RP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: Precision Resistor

Element Type: Thin Film

Package Size Code: 0402

Power Rating: .1 W

Resistance Value: 1.43K  $\Omega$

Features

Industry Standards

|                            |   |
|----------------------------|---|
| Moisture Sensitivity Level | 1 |
|----------------------------|---|

Usage Conditions

|                             |              |
|-----------------------------|--------------|
| Operating Temperature Range | -55 – 155 °C |
| Temperature Coefficient     | ±25 ppm/°C   |

Electrical Characteristics

|                             |                           |
|-----------------------------|---------------------------|
| Operating Voltage           | 25 V                      |
| Power Rating                | .1 W                      |
| Resistance Value            | 1.43K $\Omega$            |
| Resistance Class            | 1k $\Omega$ – 1M $\Omega$ |
| Passive Component Tolerance | .1 %                      |

Product Type Features

|                   |                    |
|-------------------|--------------------|
| Resistor Type     | Precision Resistor |
| Element Type      | Thin Film          |
| Package Size Code | 0402               |



Configuration Features

|                     |   |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Termination Features

|                                         |        |
|-----------------------------------------|--------|
| Surface Mount Resistor Termination Type | Solder |
| Number of Terminations                  | 2      |

Dimensions

|                |                |
|----------------|----------------|
| Product Height | .3 mm[.012 in] |
| Product Length | 1 mm[.039 in]  |
| Product Width  | .5 mm[.02 in]  |

Packaging Features

|                  |                |
|------------------|----------------|
| Packaging Method | Taped & Reeled |
|------------------|----------------|

Other

|                    |           |
|--------------------|-----------|
| EU RoHS Compliance | Compliant |
| EU ELV Compliance  | Compliant |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Reflow solder capable to 260°C                                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous

RP73PF1E1K43BTD

Surface Mount Precision Resistor, Thin Film, 0402, .1 W, 1.43K ohm, .1 %, ±25 ppm/°C, Solder, 2 Terminations, Height .3 mm [.012 in], Holsworthy RP73



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2-2176308-7  
RP 1E 0.1W 249K 0.1% 25PPM 5K RL

TE Part # 2176308-5  
RP 1E 0.1W 147K 0.1% 25PPM 5K RL

TE Part # 1625867-2  
RP 1J 0.166W 10K 0.1% 25PPM 1K RL

TE Part # 2176093-5  
RP 2A 0.25W 10K 0.1% 25PPM 1K RL

TE Part # 1-2176092-8  
RP 2A 0.25W 1K0 0.1% 25PPM 1K RL

Also in the Series | [Holsworthy RP73](#)

Surface Mount Resistors(4227)

Customers Also Bought

TE Part #2-2176338-3  
CRGCQ 0402 4K7 5%

TE Part #3-2176325-7  
CRGP 0402 10K 1%

TE Part #9-2176306-3  
RP 1E 0.1W 10K5 0.1% 25PPM 5K RL

TE Part #1-2176306-7  
RP 1E 0.1W 1K69 0.1% 25PPM 5K RL

RP73PF1E1K43BTD

Surface Mount Precision Resistor, Thin Film, 0402, .1 W, 1.43K ohm, .1 %, ±25 ppm/°C, Solder, 2 Terminations, Height .3 mm [.012 in], Holsworthy RP73



TE Part #2-2176306-2  
RP 1E 0.1W 1K91 0.1% 25PPM 5K RL

TE Part #2-2176307-7  
RP 1E 0.1W 23K2 0.1% 25PPM 5K RL

TE Part #7-1879131-2  
RN 0402 10K2 0.1% 10PPM 5K RL

TE Part #9-2176306-6  
RP 1E 0.1W 11K3 0.1% 25PPM 5K RL

TE Part #6-2176307-0  
RP 1E 0.1W 51K1 0.1% 25PPM 5K RL

TE Part #4-2176391-0  
RQ 1206 31K6 0.1% 10PPM 5K RL

Documents

Product Drawings

RP 1E 0.1W 1K43 0.1% 25PPM 5K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-2176306-0\_BA.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-2176306-0\_BA.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-2176306-0\_BA.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RP73-0915

English