




MAG-MATE

TE Internal #: 1217529-1
Tab, 4.75 mm [.187 in] Tab Width, .05 – .13 mm Magnet Wire, 44 – 36 AWG Magnet Wire, Tin Plating, MAG-MATE, Magnet Wire
Terminals

[View on TE.com >](#)

Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Tab**
Mating Tab Width: **4.75 mm [.187 in]**
Mating Tab Thickness: **.51 mm [.02 in]**
Compatible With Cavity Size: **Special**
Magnet Wire Size: **44 – 36 AWG**

Features

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Quantity	5000
Packaging Method	Package, Reel/Carton

Dimensions

Terminal Height	17.53 mm[.69 in]
Magnet Wire Size	.05 – .13 mm
Stock Thickness (Magnet Wire Side)	.25 mm[.01 in]
Product Length	22.31 mm[.878 in]

Product Type Features

Compatible With Discrete Wire Type	Solid, Magnet Wire
------------------------------------	--------------------

Body Features

Compatible With Cavity Size	Special
-----------------------------	---------



Contact Features

Magnet Wire Terminal Type	Tab
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Plating Material	Tin
Terminal Orientation	Straight

Mechanical Attachment

Mating Retention Type	Dimple
-----------------------	--------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-62511-1
MAG-MATE 22-20 187 F TAB TPBR

TE Part # 2238087-1
MAG-MATE TAB 34-33 CU / 33-31 AL TPBR

TE Part # 63255-1
MAG-MATE 187FAST TAB 0198TPBR

TE Part # 1742242-1
TAB,187 FASTON,LP,MAG-MATE

TE Part # 63675-4
POST 024X020 MINI MAG MATE

TE Part # 62780-1
MINI MAG-MATE 36-44 010 TPBR

TE Part # 1742160-1
TAB,187 FASTON,MAG-MATE

Also in the Series | MAG-MATE

Insertion & Extraction Tools(6)

Magnet Wire Terminals(329)

PCB Terminals(1)

Customers Also Bought


TE Part #917727-1
2.5 S.D.L. P/HDR ASY 7P H/PRO.

TE Part #917785-1
2.5 S.D.L POST HDR ASY 7P STD


TE Part #316227-1
2.5 S.D.L HI-PRO V 8P ON/TAPE

TE Part #5-1376383-1
5.0 POWER KEY CONNECTOR 3P HEA






TE Part #175578-1
PL 187 HOUSING RECEPTACLE



TE Part #5-1376385-1
5.0 POWER KEY CONNECTOR 6P HEA



TE Part #316222-1
2.5 S.D.L HI-PRO V 3P ON/TAPE



TE Part #1318376-1
SMARTEC CONN DUST COVER



TE Part #172761-1
PL 250 FLAG REC 18-22 0.40 X 49.2 PTBR



TE Part #937195-4
SHEAR,FLOAT FRONT

Documents

Product Drawings
MINI MAG-MATE 187 TAB

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_1217529-1_F.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_1217529-1_F.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1217529-1_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
Magnet Wire Terminals & Splices

English

Product Specifications
Application Specification

English