

E/UK-NS 35 - End bracket



1202577

<https://www.phoenixcontact.com/us/products/1202577>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



End clamps, for supporting the ends of double-level and three-level terminal blocks, width: 10 mm, color: gray

Commercial data

Item number	1202577
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE07
Product key	BE7111
Catalog page	Page 548 (C-3-2019)
GTIN	4017918017927
Weight per piece (including packing)	9.767 g
Weight per piece (excluding packing)	9.173 g
Customs tariff number	39269097
Country of origin	IN

E/UK-NS 35 - End bracket

1202577

<https://www.phoenixcontact.com/us/products/1202577>



Technical data

Product properties

Product type	End bracket
--------------	-------------

Dimensions

Width	9.5 mm
Height	48.6 mm
Depth	32.8 mm
Depth on NS 35/7,5	35 mm
Length	48.6 mm

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 35/7,5
	NS 35/15

E/UK-NS 35 - End bracket



1202577

<https://www.phoenixcontact.com/us/products/1202577>

Classifications

ECLASS

ECLASS-11.0	27141135
ECLASS-12.0	27141135
ECLASS-13.0	27250302

ETIM

ETIM 9.0	EC001041
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

E/UK-NS 35 - End bracket



1202577
<https://www.phoenixcontact.com/us/products/1202577>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com