



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Cable Clamp Kit**

Primary Product Material: **Nylon**

Primary Product Color: **Black**

Compatible With Connector Shell Size: **17**

Cable Entry Diameter: **17.86 mm [.703 in]**

Features

Housing Features

Compatible With Connector Shape	Circular
Body Orientation	Straight

Product Type Features

Strain Relief Accessory Type	Cable Clamp Kit
------------------------------	-----------------

Body Features

Primary Product Material	Nylon
Primary Product Color	Black

Operation/Application

Compatible With Connector Shell Size	17
Shielded	No

Dimensions

Cable Entry Diameter	17.86 mm[.703 in]
----------------------	-------------------

Mechanical Attachment

Thread Size	15/16-20
-------------	----------



Industry Standards

UL Flammability Rating	UL 94V-1
------------------------	----------

Packaging Features

Packaging Method	Bulk
Packaging Quantity	100

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 213902-3
CPC CABLE CLAMP KIT,LRG,SZ 17


Also in the Series | AMP CPC




Connector Backshells(1)



Connector Caps & Covers(16)




Connector Contacts(6)




Connector Seals & Cavity Plugs(35)



Connector Strain Relief(60)



Insertion & Extraction Tools(1)



Power Contacts(6)


Customers Also Bought



TE Part #1-1564297-6
31POS, MIXED,REC HSG,ASSY



TE Part #CAT-C4962-CH8172
Circular DIN Housings



TE Part #1241581-1
JUN-POW-TIM HOUSING 17POS



TE Part #CAT-H3399-CH8172
Heavy Duty Sealed Connector Series Housings




TE Part #213893-2
CPC RECPT SEALED SIZE 17-10



TE Part #185793-1
90 DEG CAP CORRUGTD TUBE



TE Part #963245-1
EINZELLEIT-DICHTUNG



TE Part #962875-1
MT2 REC 1.6 Contact SWS Sn



Documents

Product Drawings

CPC CBL CLMP KIT,LRG,SZ17,BULK

English

CAD Files

Customer View Model

ENG_CVM_213902-2_B.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_213902-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_213902-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Agency Approvals

CSA Certificate

English

CSA Certificate

English