



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 843477-1
TOOL, EXTRACTION RESET

Also in the Series | [AMPMODU 50/50 Grid](#)

Board-to-Board Headers & Receptacles(193)

Connector Caps & Covers(7)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(193)

Ribbon Cable Connectors(21)

Customers Also Bought

TE Part #NB15714001
RNF-150-1/4-0-SP

TE Part #NB16212001
RW-175-1/16-X-STK

TE Part #878462-000
S1125-KIT-1

TE Part #625160-000
D-110-41



TE Part #448859-000
D-1744-01



TE Part #NB16572001
RW-175-3/32-X-STK

Documents

Product Drawings

20 50/50 GRID CABLE RECPT

English

CAD Files

Customer View Model

ENG_CVM_CVM_104893-2_H.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_104893-2_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_104893-2_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English