

TXR18AB45-1806AI

✓ ACTIVE

RAYCHEM | RAYCHEM TXR

TE Internal #: 572613-000

Ruggedized, Backshell, .2 – 7.9 mm [.01 – .31 in] Cable Entry,
Aluminum, 45°, Shell Size 18, Entry Size 05, RAYCHEM TXR

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Backshells



Connector Backshell Product Style: **Ruggedized**

Connector Backshell Product Type: **Backshell**

Cable Entry Diameter: **.2 – 7.9 mm [.01 – .31 in]**

Primary Product Material: **Aluminum**

Body Orientation: **45°**

Features

Industry Standards

Connector Detail Specification Number	AS31001, AS31061, AS31011, AS31071
---------------------------------------	------------------------------------

Usage Conditions

Salt Spray Resistance	500 Hr
Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]

Body Features

Primary Product Color	Olive Drab
Primary Product Material	Aluminum
Primary Product Plating Material	Cadmium (AMS-QQ-P-416, Type II, Class 3)

Dimensions

Product Length	44.3 mm[1.74 in]
Compatible Cable Diameter Range	4 – 6.4 mm[.156 – .25 in]
Cable Entry Diameter	.2 – 7.9 mm[.01 – .31 in]

Product Type Features

Termination Device Included	TR06AI
Connector Backshell Product Style	Ruggedized
Connector Backshell Product Type	Backshell
Termination Device Type	Tinel-Lock Adapter, Tinel-Lock Ring, Side-Entry Tinel-Lock Ring



Housing Features

Body Orientation	45°
Compatible With Connector Shape	Circular

Operation/Application

Compatible With Connector Shell Size	18
--------------------------------------	----

Other

Connector Interface Specification	AS50151 Class A,E,F,R Less ENDBELL, Solder Contact
TE Connector Interface Code	18
Entry Size Code	05
EU RoHS Compliance	Not Compliant
EU ELV Compliance	Not Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (.3% in BODY & NUT) Cd (3% in BODY & NUT) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 173643-000
RH-3960-1-TINEL-KIT-120V

Also in the Series | RAYCHEM TXR

Circular Connector Backshells & Clamps(2043)

Connector Backshells(2043)

Ruggedized Backshells & Adapters (2043)

Customers Also Bought

TE Part #CAT-D9934-A83A
DYNAMIC 5000 REC AND TAB HSG

TE Part #CAT-D9934-A83
Contact: Component To Wire ; 20-45A , 20-8 wire size

TE Part #1-1318114-9
DYNAMIC D-2100 TAB HSG 20P P/M

TE Part #4-1473562-4
RITS CONN. PLUG ASSY 4P GREEN

TE Part #1871745-1
DYNAMIC D1000 REC CONT 2L PRE TIN L/P

TE Part #174779-1
PL 110 HOUSING RECEPTACLE

TE Part #174778-1
PL 110 REC TERMINAL 20-16 AWG PTPB

TE Part #036705-000
TXR18AB90-1806AI

Documents



Product Drawings

TXR18AB45-1806AI

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_572613-000_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_572613-000_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_572613-000_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1654025-5_sec6_Adapters

English

Product Specifications

General Information Package for Tinel-Lock Adapters

English

Braid termination using a Tinel Lock Ring installed using a resistance heater.

French

Braid termination using a Tinel Lock Ring installed using a resistance heater.

English

PERFORMANCE SPECIFICATION Tinel-Lock Rings, Heat Recoverable for Braid Termination

English

General Harness Repair Manual

English

ASSEMBLY GUIDE for Tinel -Lock Rings, Heat Recoverable for Braid Temination

English

Product Specification

English