




Transfer or duplication of this document as well as the utilisation or communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved in case of patent, utility model or design patent registrations. Tolerance specifications do not include clearances inherent in the design.

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadensersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Designeintragung vorbehalten. Bearbeitungs Spiel ist in den Toleranzangaben nicht berücksichtigt.




socket face female



*The drawing represents connector with 5 positions. At reduced number of positions, the number of holes is reduced accordingly

delivering status



1:1

Recommended solder paste thickness 150 µm

Typ	Pin [mm]	Hole □ [mm]	Residual ring □ [mm]	Template □ [mm]
Contact	See brochure "Connectors for SMT production"			
Shielding Pin	0.8x0.2	1.1	2.1	2

 DIN A3		document-no. / ri 097100740 / 02	article-no.	scale 2:1	- Simplified representation - Document excluded from change process - Linear dimensions [mm]
		date 06.09.23	document-type TECDOC 2D_Productdrawing		
		description SACC-CI-M12FS-4CON-SH TOR...			
page 1	of 1				

- EN ISO 291 23/50