

RP73D2B200KBTG

✓ ACTIVE

Holsworthy | Holsworthy RP73


TE Internal #: 4-1879265-6

Surface Mount Precision Resistor, Thin Film, 1206, .25 W, 200K ohm,
.1 %, ±15 ppm/°C, Solder, 2 Terminations, Height .55 mm [.022 in],
Holsworthy RP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**
Element Type: **Thin Film**
Package Size Code: **1206**
Power Rating: **.25 W**
Resistance Value: **200K Ω**

Features

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Electrical Characteristics

Operating Voltage	200 V
Power Rating	.25 W
Resistance Value	200K Ω
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	.1 %

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	1206

Configuration Features

Number of Resistors	1
---------------------	---

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm[.022 in]
----------------	-----------------



Product Length	3.05 mm[.12 in]
Product Width	1.55 mm[.061 in]

Usage Conditions

Temperature Coefficient	±15 ppm/°C
-------------------------	------------

Packaging Features

Packaging Method	Cut Tape Length
------------------	-----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

RP73D2B200KBTG


Surface Mount Precision Resistor, Thin Film, 1206, .25 W, 200K ohm, .1 %, ±15 ppm/°C, Solder, 2 Terminations, Height .55 mm [.022 in], Holsworthy RP73




TE Part # 2-1879747-4
RP 1J 110K 0.1% 15PPM CUT LENGTH




TE Part # 5-1879267-0
RP 2B 1M0 0.1% 15PPM 1K RL



TE Part # 9-1879252-4
RP 2B 10R 0.1% 15PPM CUT LENGTH



TE Part # 2-1879279-6
RP 2A 75K 0.1% 15PPM 1K RL



TE Part # 5-1879743-7
RP 1J 18R2 0.1% 15PPM CUT LENGTH

Also in the Series | [Holsworthy RP73](#)




[Surface Mount Resistors\(4227\)](#)

Customers Also Bought



TE Part #7-1625963-9
HSA5 3R3 5%



TE Part #6862-201-16278
CONT SOC




TE Part #1-770182-1
09P MINI UMNL ASSY VO SNAU LF



TE Part #770249-3
UMNL II SOK PTPPHBZ LP 12-14



TE Part #3-1623773-2
C10 6R8 5% (LOOSE)




TE Part #5-1462039-6
IM06PGR=IM RELAY 140mW 12V



TE Part #3-2176341-1
CRGCO 0805 3K3 1%



TE Part #2-1393561-9
V42254A 262V 19=SUB D SCHRAUBE



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1879265-6_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1879265-6_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1879265-6_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English

RP73-0915

English