



Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Insulating Accessories



Insulating Accessory Type: **Safety Cover**  
Compatible With Block or Strip Type: **Screw Clamp Terminal Blocks**  
Operating Temperature Range: **-55 – 110 °C [ -67 – 230 °F ]**  
EU RoHS Compliance: **Compliant**  
EU ELV Compliance: **Compliant**

Features

Industry Standards

IP Rating	IP20
UL Flammability Rating	UL 94V-2

Body Features

Primary Product Color	Clear
Product Weight	3.1 g[.109 oz]
Primary Product Material	Polycarbonate

Dimensions

Product Spacing	10 mm[.394 in]
Product Depth	25.83 mm[1.017 in]
Product Height	54.06 mm[2.128 in]

Usage Conditions

Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Product Type Features

Insulating Accessory Type	Safety Cover
---------------------------	--------------

Operation/Application

Compatible With Block or Strip Type	Screw Clamp Terminal Blocks
-------------------------------------	-----------------------------



Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: UV-329 (.5% in Component Part) <b>Article Safe Usage Statements:</b> Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1SNK512010R0000  
ZS25



TE Part # 1SNK512020R0000  
ZS25-BL



TE Part # 1SNK510030R0000  
ZS16-OR



TE Part # 1SNK510020R0000  
ZS16-BL



TE Part # 1SNK512150R0000  
ZS25-PE



TE Part # 1SNK512060R0000  
ZS25-YL




TE Part # 1SNK510010R0000  
ZS16

Also in the Series | ENTRELEC SNK



Modular Terminal Blocks(319)



Terminal Block & Strip Conducting  
Accessories(67)



Terminal Block & Strip Insulating  
Accessories(31)

Customers Also Bought



TE Part #2306129-1  
COVER, LIGHT CONTROL, 76MM  
DIA., TALL



TE Part #2213730-1  
LIGHT CONTROLLER BASE  
ASSEMBLY, 76MM DIA



TE Part #1-2328823-1  
LUMAWISE S 80MM DIA DOME  
CLEAR LOW



TE Part #1SNK508410R0000  
ZS4-SF1



TE Part #1SNK510150R0000  
ZS16-PE



TE Part #1SNK900607R0000  
LH-R1



TE Part #1SNK510020R0000  
ZS16-BL



TE Part #1SNK512010R0000  
ZS25



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1SNK900621R0000\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1SNK900621R0000\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1SNK900621R0000\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PL10

English

SNK SERIES TERMINAL BLOCKS

English

ENTRELEC Terminal Blocks Catalogue (RUS)

ENTRELEC Terminal Block - Master Catalog

ENTRELEC Terminal Block - Master Catalog

English