

ME B-SA/NS 35 - Cover

2935959

<https://www.phoenixcontact.com/us/products/2935959>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Terminal cover, 1 strip covers up to 12 terminal points, for ME-BUS male side, (female side)



Your advantages

- Easy, tool-free mounting
- Flammability rating V0 in accordance with UL 94

Commercial data

| | |
|--------------------------------------|---------------------|
| Item number | 2935959 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | AC08 |
| Product key | ACHACZ |
| Catalog page | Page 692 (C-1-2013) |
| GTIN | 4017918611668 |
| Weight per piece (including packing) | 5.24 g |
| Weight per piece (excluding packing) | 4.67 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

ME B-SA/NS 35 - Cover

2935959

<https://www.phoenixcontact.com/us/products/2935959>



Technical data

Product properties

| | |
|------------------------------|---|
| Product type | Filler plug |
| Housing type | DIN rail housing |
| Housing series | ME |
| Type | For ME-BUS connector side (female side) |
| Ventilation openings present | no |

Dimensions

| | |
|---------------------------------|---------|
| Width | 14.5 mm |
| Height | 91.1 mm |
| Depth | 17.9 mm |
| Depth from top edge of DIN rail | 15.2 mm |

Material specifications

| | |
|--|------------------|
| Color (Housing) | green (RAL 6021) |
| Flammability rating according to UL 94 | V0 |
| Housing material | PA |
| Surface characteristics | untreated |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Max. IP code to attain | IP20 |
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

Mounting

| | |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

ME B-SA/NS 35 - Cover

2935959

<https://www.phoenixcontact.com/us/products/2935959>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2935959>



UL Recognized

Approval ID: E240868

ME B-SA/NS 35 - Cover

2935959

<https://www.phoenixcontact.com/us/products/2935959>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27182702 |
| ECLASS-13.0 | 27190605 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

ME B-SA/NS 35 - Cover

2935959

<https://www.phoenixcontact.com/us/products/2935959>



Environmental product compliance

| | |
|---|--|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com