



P	LTR	DESCRIPTION	DATE	DWN	APVD
	C 1	NOTE 1 0.76 µm PLATING UPDATE (PdNi+AuFLASH)	14 JUL 2023	BGC	PS

POS. PER ROW	L +0.3 -0.6	PART NUMBER	POS. PER ROW	L +0.3 -0.6	PART NUMBER
-	-	-	26	66.04	2-829 492-6
2	5.08	829 492-2	27	68.58	2-829 492-7
3	7.62	3-829 492-3	28	71.12	2-829 492-8
4	10.16	4-829 492-4	29	73.66	2-829 492-9
5	12.70	5-829 492-5	30	76.20	3-829 492-0
6	15.24	6-829 492-6	31	78.74	3-829 492-1
7	17.78	7-829 492-7	32	81.28	3-829 492-2
8	20.32	8-829 492-8	33	83.82	3-829 492-3
9	22.86	9-829 492-9	34	86.36	3-829 492-4
10	25.40	1-829 492-0	35	88.90	3-829 492-5
11	27.94	1-829 492-1	36	91.44	3-829 492-6
12	30.48	1-829 492-2	37	93.98	3-829 492-7
13	33.02	1-829 492-3	38	96.52	3-829 492-8
14	35.56	1-829 492-4	39	99.06	3-829 492-9
15	38.10	1-829 492-5	40	101.60	4-829 492-0
16	40.64	1-829 492-6	41	104.14	4-829 492-1
17	43.18	1-829 492-7	42	106.68	4-829 492-2
18	45.72	1-829 492-8	43	109.22	4-829 492-3
19	48.26	1-829 492-9	44	111.76	4-829 492-4
20	50.80	2-829 492-0	45	114.30	4-829 492-5
21	53.34	2-829 492-1	46	116.84	4-829 492-6
22	55.88	2-829 492-2	47	119.38	4-829 492-7
23	58.42	2-829 492-3	48	121.92	4-829 492-8
24	60.96	2-829 492-4	49	124.46	4-829 492-9
25	63.50	2-829 492-5	50	127.00	5-829 492-0




1 MATING SIDE: MIN 0.76 µm (PdNi + Au FLASH) BY AREA "F" OVER 1.27 µm NICKEL
(Alternative plating - Min 0.76 µm Au OVER 1.27 µm Ni)

SOLDER SIDE: MIN. 3.0 µm TIN OVER 1.27 µm NICKEL


2 OBSOLETE PARTS: OBSOLETE C IS STREAMLINING PER D.RENAUD/D.SINISI

3 OBSOLETE

1	CuZn	CONTACT PIN KONTAKTSTIFT
COLOUR BLACK	PCT	PIN HOUSING STIFTGEHAEUSE
REMARK BEMERKUNG	MATERIAL	DESCRIPTION BEZEICHNUNG



PC BOARD LAYOUT
LEITERPLATTEN-
ANSCHLUSSBILD

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN F.MUELLER 06NOV1989		 TE Connectivity							
DIMENSIONS: mm		CHK M.SCHAARSCHMIDT 06NOV1989									
		APVD -		NAME AMPMODU II PIN HEADER TRIPLE ROW							
		PRODUCT SPEC 108-18012									
		APPLICATION SPEC -									
		WEIGHT -									
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm				SIZE A 3		CAGE CODE 00779		DRAWING NO C-829492		RESTRICTED TO -	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±											
MATERIAL SEE TABLE		FINISH SEE TABLE		CUSTOMER DRAWING		SCALE 5:1		SHEET 1 OF 1		REV C 1	