

D-UKK 3-MSTB-5,08 L - End cover

2770914

<https://www.phoenixcontact.com/us/products/2770914>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



End cover, pitch: 5.08 mm, depth: 42.3 mm, width: 2.5 mm, height: 50 mm, number of positions: 1, color: gray

Commercial data

Item number	2770914
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE19
Product key	BE1Z1X
Catalog page	Page 324 (CL-2005)
GTIN	4017918068134
Weight per piece (including packing)	4.08 g
Weight per piece (excluding packing)	4.08 g
Customs tariff number	85389099
Country of origin	DE

D-UKK 3-MSTB-5,08 L - End cover



2770914

<https://www.phoenixcontact.com/us/products/2770914>

Technical data

Product properties

Product type	End cover
Product family	DECKEL + RZ + DP
Number of positions	1
Pitch	5.08 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0

Dimensions

Width	2.5 mm
Height	50 mm
Depth	42.3 mm
Pitch	5.08 mm

D-UKK 3-MSTB-5,08 L - End cover



2770914

<https://www.phoenixcontact.com/us/products/2770914>

Classifications

ECLASS

ECLASS-11.0	27141133
ECLASS-12.0	27141133
ECLASS-13.0	27250301

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

D-UKK 3-MSTB-5,08 L - End cover



2770914

<https://www.phoenixcontact.com/us/products/2770914>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com