


Passive Components > Resistors > Surface Mount Resistors

Resistor Type: **Current Sensing Resistor**Element Type: **Thick Film**Package Size Code: **2512**Power Rating: **1 W**Resistance Value: **.018 Ω**

Features

Usage Conditions

Operating Temperature Range **-55 – 155 $^{\circ}$ C**Temperature Coefficient **± 600 ppm/ $^{\circ}$ C**

Product Type Features

Resistor Type **Current Sensing Resistor**Element Type **Thick Film**Package Size Code **2512**

Configuration Features

Number of Resistors **1**

Electrical Characteristics

Power Rating **1 W**Resistance Value **.018 Ω** Resistance Class **Up to 1k Ω** Passive Component Tolerance **1 %**

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.6 mm [.024 in]
Product Length	6.35 mm [.25 in]
Product Width	3.1 mm [.122 in]

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An


Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 2176601-7
RLC73V 3A R018 1% 4K RL

Also in the Series | CGS RLC73



Surface Mount Resistors(2392)

Customers Also Bought



TE Part #1-6609006-7
15EEJ1=F8021 S0



TE Part #2176230-2
3522 1R0 5% 3W



TE Part #8-1676481-1
CPF 0603 18K 0.1% 25PPM 1K RL



TE Part #1-640445-6
16P MTA156 HDR ASSY FL/STR SN



TE Part #8-1393239-8
RT314F24



TE Part #926883-1
UNIVERSAL M-N-L PIN



TE Part #1-1879417-3
CPF 0603 560K 0.1% 25PPM 1K RL



TE Part #4-1879351-2
RR01 5% 150K AMMO



Documents

Product Drawings

[RLC73V 3A R018 1% 1K RL](#)

English

CAD Files

[Customer View Model](#)

[ENG_CVM_CVM_2176603-7_BA.3d_igs.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_2176603-7_BA.3d_stp.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_2176603-7_BA.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SMD Low Ohmic - Current Sense Resistors - Type RLC73 Series](#)

English