

CK4,0-ED-10,00BU AG - Crimp contact



1586183

<https://www.phoenixcontact.com/us/products/1586183>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, contact diameter: 4 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 10 mm² ... 10 mm², AWG 8

Commercial data

Item number	1586183
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BF65
Product key	BF7AIE
Catalog page	Page 511 (C-2-2019)
GTIN	4046356359597
Weight per piece (including packing)	2.662 g
Weight per piece (excluding packing)	2.46 g
Customs tariff number	85366990
Country of origin	DE

CK4,0-ED-10,00BU AG - Crimp contact



1586183

<https://www.phoenixcontact.com/us/products/1586183>

Technical data

Notes

General	for HC-M-02, HC-M-03, HC-M-03/04, HC-M-04, HC-Q02, HC-Q03, HC-Q04, and HC-COM-Q4/2 contact carriers
---------	---

Mounting

Assembly note	The quality of a crimp connection is determined by DIN EN 60352-2.
---------------	--

Product properties

Product type	Crimp contact
Series	HC-M-03
	HC-M-03/04
	HC-M-04
	HC-K
	HC-M-02
	HC-HS
Type	Individual female contact
Contact material type	turned

Connection data

Connection method	Crimp connection
Contact connection type	Socket
Connection technology	Crimp connection
Conductor cross section	10 mm ² ... 10 mm ²
Connection cross section AWG	8
Stripping length of the individual wire	18 mm (For wire Ø ≥ 6.4 mm)
	15 mm (For wire Ø ≥ 4.3 mm)
Conductor cross section flexible	10 mm ² ... 10 mm ²

Material specifications

Contact material	Copper alloy
Contact surface material	silver-plated

Dimensions

Mechanical characteristics	
Contact diameter	4 mm

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500

Environmental and real-life conditions

CK4,0-ED-10,00BU AG - Crimp contact

1586183

<https://www.phoenixcontact.com/us/products/1586183>



Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------


CK4,0-ED-10,00BU AG - Crimp contact

1586183

<https://www.phoenixcontact.com/us/products/1586183>



Drawings



Dimensional drawing

CK4,0-ED-10,00BU AG - Crimp contact



1586183

<https://www.phoenixcontact.com/us/products/1586183>

Classifications

ECLASS

ECLASS-11.0	27440204
ECLASS-12.0	27440204
ECLASS-13.0	27440204

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK4,0-ED-10,00BU AG - Crimp contact



1586183

<https://www.phoenixcontact.com/us/products/1586183>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com