

SPECIFICATIONS

Mechanical

Contact Retention Force: 0.10kg min.

Durability : 60 Cycles

Electrical

Voltage Rating: 25V

Current Rating: 0.5A

Contact Resistance: 60mΩ max.

Dielectric Withstanding Voltage: 250V AC/1 min.

Insulation Resistance: 100MΩ

Physical

Housing: Thermoplastic, UL 94V-0 rated in Black Color

Contact: Copper alloy

Plating: See "ORDERING INFORMATION"

Metal Spring: Copper alloy

Operating Temperature: -55℃ to +85℃

DDRIV SO DIMM Socket

AS Series

9.2 mm Height


SMT Type

0.50mm Pitch

260 Pos.



DRAWING



ORDERING INFORMATION

PRODUCT NO.: A S A A8 2 * - E A * B 0 - * H

Memory Module Socket

Horizontal Type

Single Row

No. Of Pos.

A8=260 Pos.

SMT Type

Contact Area Plating

1=Gold Flash

Y=5u"Gold Plating

6=10u"Gold Plating

7=15u"Gold Plating

3=30u"Gold Plating

H=HALOGEN
/LEAD FREE

Package Code

4=Soft Tray

7=Tape Reel

0=Normal Type

B=BLACK COLOR

S=Standard

R=Reverse

A=9.2mm Height

E=DDR SODIMM

AS0A82*-EASB0- *H	35.50	28.50
AS0A82*-EARB0- *H	28.50	35.50
P/ N	DIM.A	DIM.B