








2~4P



SECTION A-A



Technical Index:

1. Temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 3.0A.
4. Contact resistance: $\leq 20\text{m}\Omega$.
5. Withstanding voltage: 1000V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.

适用线路板(PCB LAYOUT)

序号	品名	材质
1	XH2.5 胶芯	PA66 UL94V-2 Beige
2	XH2.5 弯针 端子	Copper Alloy/ Tin Plating

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: HA2.5 弯针带扣	
DECIMALS:		PAR	WAFER-HA2.54-NPWZ-Y62
ANGLES:		DWN	
X.: ± 0.50		CHKD	
X'.: $\pm 5^{\circ}$		APVD	
.X: ± 0.20		SCALE:1:1	UNIT:MM
.XX: ± 0.10		SIZE:A4	SHEET:1F1
CUSTOMER COPY		REV:A	