




Model	高度(H)	C	D
BTB0.530-XPLBDC-M41	3.0MM	2.15	2.35
BTB0.535-XPLBDC-M41	3.5MM	2.15	2.35
BTB0.540-XPLBDC-M41	4.0MM	2.15	2.35

Model	PIN	DIM A	DIM B
BTB0.535-20PLBDC-M41	20	8.20	4.50
BTB0.535-22PLBDC-M41	22	8.70	5.00
BTB0.535-30PLBDC-M41	30	10.70	7.00
BTB0.535-34PLBDC-M41	34	11.70	8.00
BTB0.535-40PLBDC-M41	40	13.20	9.50
BTB0.535-50PLBDC-M41	50	15.70	12.00
BTB0.535-60PLBDC-M41	60	18.20	14.50
BTB0.535-70PLBDC-M41	70	20.70	17.00
BTB0.535-80PLBDC-M41	80	23.20	19.50
BTB0.535-100PLBDC-M41	100	28.20	24.50
BTB0.535-120PLBDC-M41	120	33.20	29.50

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		 TITLE: AXK 0.50mm BTB SOCKET	
DECIMALS:	ANGLES:	PAR	BTB0.535-XPLBDC-M41
.X $\pm$ 0.35	$\pm 1^{\circ}$	DWN	
.XX $\pm$ 0.25		CHKD	
.XXX $\pm$ 0.10		APVD	
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A