







型号	CKT	A	B
WAFER-MBX3.0-02PJK-MB	2*1	0.00	5.30
WAFER-MBX3.0-04PJK-MB	2*2	3.00	8.30
WAFER-MBX3.0-06PJK-MB	2*3	6.00	11.30
WAFER-MBX3.0-08PJK-MB	2*4	9.00	14.30
WAFER-MBX3.0-10PJK-MB	2*5	12.00	17.30
WAFER-MBX3.0-12PJK-MB	2*6	15.00	20.30
WAFER-MBX3.0-14PJK-MB	2*7	18.00	23.30
WAFER-MBX3.0-16PJK-MB	2*8	21.00	26.30
WAFER-MBX3.0-18PJK-MB	2*9	24.00	29.30
WAFER-MBX3.0-20PJK-MB	2*10	27.00	32.30
WAFER-MBX3.0-22PJK-MB	2*11	30.00	35.30
WAFER-MBX3.0-24PJK-MB	2*12	33.00	38.30

技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. 额定电压: 250V AC, DC.
3. 耐电压: 1500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 5A AC, DC.

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuo XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			
DECIMALS:	ANGLES:	TITLE: MX3.0 双排 母座胶壳	
X.X $\pm$ 0.30	X. $^{\circ}$ $\pm$ 5 $^{\circ}$	PAR	WAFER-MX3.0-NPJK-MB
X.XX $\pm$ 0.25	X.X $^{\circ}$ $\pm$ 1 $^{\circ}$	DWN	
X.XXX $\pm$ 0.15		CHKD	
		APVD	
CUSTOMER COPY		SCALE:A	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A