




Technical Index:

1. Temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.

2. Rated voltage: 200V




DC/AC(rms).

3. Rated current: 2.0A.

4. Contact resistance: $\leq 25\text{m}\Omega$.

5. Withstanding voltage: 500V

AC/minute.

6. Insulation resistance: $\geq 1000\text{M}\Omega$.

适用线路板(PCB LAYOUT)

序号	品名	材质
1	PH2.0 直针 胶芯	PA66 UL94V-2 Beige
2	PH2.0 直针 端子	Copper Alloy/ Tin Plating

Part No	Pin	A	B
WAfer-PH2.0-2PZZ-Y62	2	2.00	6.00
WAfer-PH2.0-3PZZ-Y62	3	4.00	8.00
WAfer-PH2.0-4PZZ-Y62	4	6.00	10.00
WAfer-PH2.0-5PZZ-Y62	5	8.00	12.00
WAfer-PH2.0-6PZZ-Y62	6	10.00	14.00
WAfer-PH2.0-7PZZ-Y62	7	12.00	16.00
WAfer-PH2.0-8PZZ-Y62	8	14.00	18.00
WAfer-PH2.0-9PZZ-Y62	9	16.00	20.00
WAfer-PH2.0-10PZZ-Y62	10	18.00	22.00
WAfer-PH2.0-11PZZ-Y62	11	20.00	24.00
WAfer-PH2.0-12PZZ-Y62	12	22.00	26.00
WAfer-PH2.0-13PZZ-Y62	13	24.00	28.00
WAfer-PH2.0-14PZZ-Y62	14	26.00	30.00
WAfer-PH2.0-15PZZ-Y62	15	28.00	32.00
WAfer-PH2.0-16PZZ-Y62	16	30.00	34.00
WAfer-PH2.0-17PZZ-Y62	17	32.00	36.00
WAfer-PH2.0-18PZZ-Y62	18	34.00	38.00
WAfer-PH2.0-19PZZ-Y62	19	36.00	40.00
WAfer-PH2.0-20PZZ-Y62	20	38.00	42.00

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: PH2.0 直针	
DECIMALS: X.:±0.50 .X:±0.20 .XX:±0.10		PAR WAfer-PH2.0-NPZZ-Y62	
ANGLES: X':±5° X.X':±3° X.XX':±1°		DWN CHKD APVD	
CUSTOMER COPY		SCALE:1:1 UNIT:MM SIZE:A4	
		SHEET:1F1 REV:A	