






版次	变更摘要	日期
0	新产品发行	2021/3/01



技术指标(Technical Index):

1. 工作温度(Temperature range): $-20^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. 额定电压(Rated voltage): 30V AC/DC.
3. 额定电流(Rated current): 0.5A AC/DC.
4. 接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
5. 耐压值(Dielectricwithstanding voltage): 200V AC/minute.
6. 绝缘电阻(Insulation resistance): $\geq 100\text{M}\Omega$.
7. 适用线规(Apply to gauge): AWG#28~#32 (O.D0.6mm MAX).



一般公差 (TOLERANCE)
X. ± 0.50 XX ± 1.0
.X ± 0.20 .XXX ± 0.05
ANGLES $\pm 1^{\circ}$

Bossie (博锡)

品名 (TITLE)	0.80 Pitch C型WTB公头端子			制图 (DR)	Huangwendan
料号 (DWG.NO)	BX-0.8-DZ			校对 (CHKD)	李绍宗
比例 (SCALE)	1:1	单位 (UNITS)	mm	审核 (APPD)	黄志明
张数 (SHEET)	1 OF 1	SIZE	A4	REV	A