







D		E	F		
版次	变更摘要	日期	序号	品名	材质
0	新产品发行	2019/07/20	①	HA2.5弯针WTB胶芯	PA66 UL94V-0 米色 白色
			②	XH2.5弯针WTB端子	铜合金/表面镀锡




TYPE 1 (无K脚)



SECTION A-A

- 技术指标(Technical Index):
1. 温度范围(Temperature range): -25° C~+85° C.
 2. 额定电压(Rated voltage): 250V, AC.
 3. 额定电流(Rated current): 3.0A AC,DC.
 4. 接触电阻(Contact resistance): ≤20mΩ .
 5. 耐压值(Withstanding voltage): 1000V AC/minute.
 6. 绝缘电阻(Insulation resistance): ≥1000MΩ.



CKT	A	B	CKT	A	B
2	2.5	7.5	10	22.5	27.5
3	5.0	10.0	11	25.0	30.0
4	7.5	12.5	12	27.5	32.5
5	10.0	15.0	13	30.0	35.0
6	12.5	17.5	14	32.5	37.5
7	15.0	20.0	15	35.0	40.0
8	17.5	22.5	16	37.5	42.5
9	20.0	25.0	17	40.0	45.0



品名 (TITLE)		制图 (DR)	
HA2.5弯针WTB		ANLAN	
料号 (DWG.NO)		校对 (CHKD)	
BX-HA2.54-n*PWZ-GW		李绍宗	
比例 (SCALE)		审核 (APPD)	
1:1		黄志明	
单位 (UNITS)	mm	张数 (SHEET)	1 OF 1
尺寸 (SIZE)	A4	版本 (REV)	A

一般公差 (TOLERANCE)	
X. ±.50	.XX ±.10
.X ±.20	.XXX ±.05
ANGLES	±1°