







版次	变更摘要	日期	序号	品名	材质
0	新产品发行	2019/06/15	①	PH2.0直针WTB胶芯	米色 PA66 UL94V-0 白色 红色
			②	PH2.0弯针WTB端子	铜合金/表面镀锡



SECTION A-A




TYPE 1 (无K脚)



TYPE 2 (打K脚)

技术指标(Technical Index):

- 工作温度(Temperature range): -25° C~85° C.
- 额定电压(Rated voltage): 200V DC/AC(rms).
- 额定电流(Rated current): 2.0A.
- 接触电阻(Contact resistance): ≤25mΩ.
- 耐压值(Withstanding voltage): 500V AC/minute.
- 绝缘电阻(Insulation resistance): ≥1000MΩ.



CKT	A	B	CKT	A	B
2	2.0	6.0	12	22.0	26.0
3	4.0	8.0	13	24.0	28.0
4	6.0	10.0	14	26.0	30.0
5	8.0	12.0	15	28.0	32.0
6	10.0	14.0	16	30.0	34.0
7	12.0	16.0	17	32.0	36.0
8	14.0	18.0	18	34.0	38.0
9	16.0	20.0	19	36.0	40.0
10	18.0	22.0	20	38.0	42.0
11	20.0	24.0			



兆星精密电子 (深圳) 有限公司

品名 (TITLE)	PH2.0弯针WTB	制图 (DR)	Anlan
料号 (DWG.NO)	ZX-PH2.0-n*PWZ-GW	校对 (CHKD)	李绍宗
比例 (SCALE)	1:1	审核 (APPD)	黄志明
单位 (UNITS)	mm	张数 (SHEET)	1 OF 1
		SIZE	A4
		REV	A



一般公差 (TOLERANCE)
X. ±.50 XX ±.10
.X ±.20 .XXX ±.05
ANGLES ±1°