


|   |   |
|---|---|
| A | — |
| B | — |
| C | — |
| D | — |
| E | — |
| F | — |
| G | — |
| H | — |

| Dept | Qty |
|------|-----|
| DC   | 1   |
| ED   | 1   |
| IE   | 1   |
| ISO  | 1   |
| PD   | 1   |
| R&D  | 1   |
| SA   | 1   |
| SD   | 1   |
| QC   | 1   |
| QE   | 1   |

晨翔料号: DS1022-1x3RUF11-B



1. 电性说明:
  - 1.1 接触阻抗: 20毫欧最大
  - 1.2 耐压: 600伏交流电一分钟
  - 1.3 绝缘阻抗: 1000兆欧最小
  - 1.4 额定电流: 3安
2. 环境特性:
  - 2.1 工作温度: -40~+105° C
3. 材料:
  - 3.1 四方针: H62黄铜, 镍底镀金
  - 3.2 胶芯: PBT, 黑色, 阻燃

|                   |                   |                 |        |                                                                                                                                                    |                                                                                       |        |                              |  |
|-------------------|-------------------|-----------------|--------|----------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|--------|------------------------------|--|
| GENERAL TOLERANCE |                   | ANGLE TOLERANCE |        | PROJECTION                                                                                                                                         |  | TITLE  | 2.54mm Pin Header R/A U Type |  |
| X.                | ±0.60             | X.              | ±5°    | UNITS                                                                                                                                              | mm                                                                                    |        |                              |  |
| .X                | ±0.38             | .X              | ±3°    | SHEET SIZE                                                                                                                                         | A4                                                                                    | SERIES | DS1022 SERIES                |  |
| .XX               | ±0.25             | .XX             | ±2°    |  <b>晨翔电子有限公司</b><br><b>CONNFLY CONNFLY ELECTRONIC CO. LTD</b> |                                                                                       |        |                              |  |
| DRAWING TYPE      |                   | CUSTOMER        |        |                                                                                                                                                    |                                                                                       |        |                              |  |
| SCALE             | 1:1               | SHEET           | 1 OF 1 |                                                                                                                                                    |                                                                                       |        |                              |  |
| DRAWING NO.       | C-DS1022-XXXXXX-A |                 |        |                                                                                                                                                    |                                                                                       |        |                              |  |



晨翔电子有限公司

**CONNFLY CONNFLY ELECTRONIC CO. LTD**