


Dept	Qty
DC	1
ED	1
IE	1
ISO	1
PD	1
R&D	1
SD	1
QA	1
QC	1
QE	1

晨翔料号: DS1022-1x3RDF11-B



- 1.1 接触阻抗: 20毫欧最大
- 1.2 耐压: 600伏交流电一分钟
- 1.3 绝缘阻抗: 1000兆欧最小
- 1.4 额定电流: 3安
2. 环境特性:
 - 2.1 工作温度: -40~+105° C
3. 材料:
 - 3.1 端子: H62黄铜, 镍底镀金
 - 3.2 胶芯: PBT, 黑色, 阻燃

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	WPY 12/09/24'	~	

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	2.54mm PIN HEADER R/A TYPE	
X.	±0.60	X.	±5°	UNITS	mm	SINGLE ROW D TYPE		
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1022 SERIES	
.XX	±0.25	.XX	±2°					
DRAWING TYPE		CUSTOMER		 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD				
SCALE	1:1	SHEET	1 OF 1					
DRAWING NO.	C-DS1022-XXXXXX-A							