



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



Part No	Pin	A	B	C
A05FC-F4P-H20	4	1.50	2.60	6.40
A05FC-F5P-H20	5	2.00	3.10	6.90
A05FC-F6P-H20	6	2.50	3.60	7.40
A05FC-F7P-H20	7	3.00	4.10	7.90
A05FC-F8P-H20	8	3.50	4.60	8.40
A05FC-F9P-H20	9	4.00	5.10	8.90
A05FC-F10P-H20	10	4.50	5.60	9.40
A05FC-F11P-H20	11	5.00	6.10	9.90
A05FC-F12P-H20	12	5.50	6.60	10.40
.....		...		
A05FC-F65P-H20	65	$(60-1)*0.5$	$(60+1)*0.5+0.10$	$(60+9)*0.5-0.1$

SECTION A-A




适用线路板(PCB LAYOUT)

序号	品名	材质
1	0.5前翻胶芯(H=2.0)	LCP UL94V-0 本色
2	0.5前翻端子(H=2.0)	铜合金/表面镀锡
3	0.5前翻后盖(H=2.0)	LCP UL94V-0 黑色
4	0.5前翻焊片(H=2.0)	铜合金/表面镀锡

适用扁平线(Applicable Flat Cable)


技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^\circ\text{C} \sim +85^\circ\text{C}$ 。
3. 额定电压: 50V, AC/DC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 500M\Omega$




TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X: ± 0.30	.X': $\pm 5^\circ$	PART NO. A05FC-FNP-H20	TITLE: 0.5mm间距卧贴翻盖式下接H2.0高	
.XX: ± 0.20	.XX': $\pm 3^\circ$			
.XXX: ± 0.05	.XXX': $\pm 1^\circ$	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		SCALE
MATERILA	---	APPD: Ava		SHEET
FINISH	---			1/1

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SECTION A-A
SCALE 2:1



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X:±0.30	.X':±5°	PART NO. A05FC-FNP-H20	TITLE: 0.5mm间距卧贴翻盖式下接H2.0高		
.XX:±0.20	.XX':±3°				
.XXX:±0.05	.XXX':±1°				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/1