



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



Recommended metal mask thickness: $t=0.1$

Recommended FPC/FFC Dimensions

NOTE:

1. MATERIAL:

HOUSING: LCP (UL94V-0), COLOR: NATURAL.

CONTACTS: COPPER ALLOY.

PEG: COPPER ALLOY.

ACTUATOR: LCP (UL94-V0). COLOR:BLACK

2. *RATING:*

OPERATING VOLTAGE: 50Vrms AC.

CURRENT RATING: 0.5A.

OPERATING TEMPERATURE: $-55^{\circ}\text{C}\sim+85^{\circ}\text{C}$.

OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY

90% MAX.(NO CONDENSATION)

STORAGE TEMPERATURE RANGE: $-10^{\circ}\text{C}\sim+50^{\circ}\text{C}$.

STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90%
MAX.(NO CONDENSATION)

带 (XX) 为重点管控尺寸

Part No	Pin	A	B	C	D	E	F	G
A05FC-4RLTAG-H10	4	4.00	1.50	2.57	3.39	3.10	3.90	2.50
A05FC-5RLTAG-H10	5	4.50	2.00	3.07	3.89	3.60	4.50	3.00
A05FC-6RLTAG-H10	6	5.00	2.50	3.57	4.39	4.10	4.90	3.50
A05FC-8RLTAG-H10	8	6.00	3.50	4.57	5.39	5.10	5.90	4.50
A05FC-10RLTAG-H10	10	7.00	4.50	5.57	6.39	6.10	6.90	5.50
A05FC-12RLTAG-H10	12	8.00	5.50	6.57	7.39	7.10	7.90	6.50
A05FC-14RLTAG-H10	14	9.00	6.50	7.57	8.39	8.10	8.90	7.50
A05FC-16RLTAG-H10	16	10.00	7.50	8.57	9.39	9.10	9.90	8.50
A05FC-18RLTAG-H10	18	11.00	8.50	9.57	10.39	10.10	10.90	9.50
A05FC-20RLTAG-H10	20	12.00	9.50	10.57	11.39	11.10	11.90	10.50
A05FC-22RLTAG-H10	22	13.00	10.50	11.57	12.39	12.10	12.90	11.50
A05FC-24RLTAG-H10	24	14.00	11.50	12.57	13.39	13.10	13.90	12.50
A05FC-26RLTAG-H10	26	15.00	12.50	13.57	14.39	14.10	14.90	13.50
A05FC-28RLTAG-H10	28	16.00	13.50	14.57	15.39	15.10	15.90	14.50
A05FC-30RLTAG-H10	30	17.00	14.50	15.57	16.39	16.10	16.90	15.50
A05FC-32RLTAG-H10	32	18.00	15.50	16.57	17.39	17.10	17.90	16.50
A05FC-34RLTAG-H10	34	19.00	16.50	17.57	18.39	18.10	18.90	17.50
A05FC-40RLTAG-H10	40	22.00	19.50	20.57	21.39	21.10	21.90	20.50

TOLERANCE



深圳聚兴泰电子科技有限公司
Shenzhen Juxingtai Electronic Technology Co., Ltd

.X:±0.30	.X':±5"	PART NO. A05FC-NRLTAG-H10	TITLE: 0.5Pitch 1.0H ZIF/前插后拨式		
.XX:±0.20	.XX':±2"				
.XXX:±0.05	.XXX':±1"	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm				
MATERILA	— — —	CHED: Olivia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1