







序号	品名	材质
1	0.5mm间距芯(H2.0)	LCP UL94V-0 本色
2	0.5mm间距端子(H2.0)	铜合金/表面镀锡
3	0.5mm间距后盖(H2.0)	LCP UL94V-0 黑色
4	0.5mm间距弹片(H2.0)	铜合金/表面镀锡

技术指标:


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC/DC(等效)。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 500M\Omega$ 。



Applicable Flat Cable

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B	C
A10FC-S02FCC-H20	2	1.00	3.10	6.90
A10FC-S03FCC-H20	3	2.00	4.10	7.90
A10FC-S04FCC-H20	4	3.00	5.10	8.90
A10FC-S05FCC-H20	5	4.00	6.10	9.90
A10FC-S06FCC-H20	6	5.00	7.10	10.90
A10FC-S07FCC-H20	7	6.00	8.10	11.90
A10FC-S08FCC-H20	8	7.00	9.10	12.90
A10FC-S09FCC-H20	9	8.00	10.10	13.90
A10FC-S10FCC-H20	10	9.00	11.10	14.90
.....		...		
A10FC-S32FCC-H20	32	(32-1)*1.0	(32+1)*1.0+0.10	(32+6)*1.0-0.10



适用线路板(PCB LAYOUT)

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X: ± 0.38	.X': ± 5°	PART NO. A10FC-SNFCC-H20	TITLE: 1.0mm间距C型翻盖式下接	
.XX: ± 0.20	.XX': ± 3°		MANUFACTURE DWG	
.XXX: ± 0.05	.XXX': ± 1°			
UNITS	mm	DESIGN: Ethan		
MATERILA	— — —	CHED: Olvia		
FINISH	— — —	APPD: Ava		
			SCALE N:A	SHEET 1/1