



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SECTION A-A

Part No	Pin	A	B	C	D
A05FC-S04ECA-H20	4	1.50	2.56	7.60	5.20
A05FC-S05ECA-H20	5	2.00	3.06	8.10	
A05FC-S06ECA-H20	6	2.50	3.56	8.60	
A05FC-S07ECA-H20	7	3.00	4.06	9.10	
A05FC-S08ECA-H20	8	3.50	4.56	9.60	
A05FC-S09ECA-H20	9	4.00	5.06	10.10	
A05FC-S10ECA-H20	10	4.50	5.56	10.60	
A05FC-S11ECA-H20	11	5.00	6.06	11.10	
A05FC-S12ECA-H20	12	5.50	6.56	11.60	
.....					5.75
A05FC-S34ECA-H20	34	16.50	17.56	22.60	
A05FC-S35ECA-H20	35	17.00	18.06	23.10	
A05FC-S36ECA-H20	36	17.50	18.56	23.60	
.....					
A05FC-S60ECA-H20	60	(60-1)*0.5	(60+1)*0.5+0.06	(60+11)*0.5+0.1	



适用线路板(PCB LAYOUT)

序号	品名	材质
1	0.5拉拔胶芯(H2.0)	LCP UL94V-0 本色
2	0.5拉拔上接端子(H2.0)	铜合金/表面镀锡
3	0.5拉拔卧式后盖(H2.0)	LCP UL94V-0 黑色
4	0.5拉拔焊片(H2.0)	铜合金/表面镀锡

适用扁平线(Applicable Flat Cable)

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25°C~+85°C.
3. 额定电压: 50V, AC/DC.
4. 接触电阻: ≤0.03Ω.
5. 绝缘电阻: ≥500MΩ

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X:±0.38	.X':±5°	PART NO.	TITLE: FPC 0.5mm间距 卧式贴片上接Connector(窄扣)		
.XX:±0.20	.XX':±3°	A05FC-SNECA-H20	MANUFACTURE DWG 		
.XXX:±0.05	.XXX':±1°	DESIGN: Ethan			
UNITS	mm	CHED: Olvia			
MATERILA	— — —	APPD: Ava			
FINISH	— — —				
			SCALE	SHEET	
			N:A	1/1	