










适用扁平线(Applicable Flat Cable)

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC/DC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 500M\Omega$ 。

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B	C
A05FC-F4P-H15	4	1.50	6.20	2.53
A05FC-F5P-H15	5	2.00	6.70	3.03
A05FC-F6P-H15	6	2.50	7.20	3.53
A05FC-F7P-H15	7	3.00	7.70	4.03
A05FC-F8P-H15	8	3.50	8.20	4.53
A05FC-F9P-H15	9	4.00	8.70	5.03
A05FC-F10P-H15	10	4.50	9.20	5.53
A05FC-F11P-H15	11	5.00	9.70	6.03
A05FC-F12P-H15	12	5.50	10.20	6.53
.....				
A05FC-F60P-H15	60	(60-1)*0.5	(60+8)*0.5+0.20	(60+1)*0.5+0.03



适用线路板(PCB LAYOUT)

序号	品名	材质
1	0.5前翻胶芯(H=1.5)	LCP UL94V-0 本色
2	0.5前翻端子(H=1.5)	铜合金/表面镀锡
3	0.5前翻后盖(H=1.5)	LCP UL94V-0 黑色
4	0.5前翻焊片(H=1.5)	铜合金/表面镀锡

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X:±0.38	.X':±5°	PART NO. A05FC-FNP-H15	TITLE: 0.5mm间距卧贴翻盖式 下接H1.5高		
.XX:±0.20	.XX':±3°				
.XXX:±0.05	.XXX':±1°				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/1