

1					2					3					4					5					6					7					8							
A	Dept	晨翔3.0mm Micro ATX TYPE, 2*2PIN连接器公头, 弯插 有柱子, 黑色, 全锡																				REV.	DESCRIPTION					DRAWN					CHECKED					APPROVED				
	Qty																					A	NEW RELEASE					WPY 11/14/24'														
	DC	1																																								
	ED	1																																								
	IE	1																																								
B	ISO	1																																								
	PD	1																																								
	R&D	1																																								
	SD	1																																								
	QA	1																																								
C	QC	1																																								
	QE	1																																								
D																																										
E																																										
F																																										
G																																										
H																																										

晨翔料号: DS1073-04-2x2MRB6

9.80
7.40
3.00
3.00
10.00
3.20
1.80
3.00
3.00
4.50
SQ0.64
3.00±0.1
Ø3.00
PCB板孔尺寸参考
公差:±0.05

备注:

1. 电性说明:

1.1 耐压: 600伏交流电一分钟

1.2 绝缘阻抗: 1000兆欧最小

1.3 接触电阻: 最大30毫欧

1.4 额定电流: 3安

2. 环境特性:

2.1 工作温度: -25~+85° C

3. 材料:

3.1 胶芯: 尼龙, 黑色, 阻燃

3.2 端子: 铜合金, 镀锡

4. 产品符合欧盟RoHS环保要求

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	3.0mm Micro ATX TYPE, 2*2PIN连接器公头, 弯插 有柱子, 黑色, 全锡	
X.	±0.60	X.	±5°	UNITS	mm			
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1073-04 SERIES	
.XX	±0.25	.XX	±2°					
DRAWING TYPE		CUSTOMER		晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD				
SCALE		1:1						
DRAWING NO.		C-DS1073-04-XXXXX-A						
		SHEET	1 OF 1					