



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SECTION A-A

Part No	Pin	A	B	C
A05FC-S04FCC-H20	4	1.50	2.60	6.40
A05FC-S05FCC-H20	5	2.00	3.10	6.90
A05FC-S06FCC-H20	6	2.50	3.60	7.40
A05FC-S07FCC-H20	7	3.00	4.10	7.90
A05FC-S08FCC-H20	8	3.50	4.60	8.40
A05FC-S09FCC-H20	9	4.00	5.10	8.90
A05FC-S10FCC-H20	10	4.50	5.60	9.40
A05FC-S11FCC-H20	11	5.00	6.10	9.90
A05FC-S12FCC-H20	12	5.50	6.60	10.40
.....		...		
A05FC-S65FCC-H20	65	(60-1)*0.5	(60+1)*0.5+0.10	(60+9)*0.5-0.1




序号	品名	材质
1	0.5前翻胶芯(H=2.0)	LCP UL94V-0 本色
2	0.5前翻端子(H=2.0)	铜合金/表面镀锡
3	0.5前翻后盖(H=2.0)	LCP UL94V-0 黑色
4	0.5前翻焊片(H=2.0)	铜合金/表面镀锡

适用扁平线(Applicable Flat Cable)

技术指标:


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC/DC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 500M\Omega$ 。




适用线路板(PCB LAYOUT)

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X: ±0.30	.X': ±5°	PART NO.	TITLE: 0.5mm间距卧贴翻盖式下接H2.0高	
.XX: ±0.20	.XX': ±3°	A05FC-SNFC-H20	MANUFACTURE DWG	
.XXX: ±0.05	.XXX': ±1°	DESIGN: Ethan		
UNITS	mm	CHED: Olvia	SCALE	SHEET
MATERILA	— — —	APPD: Ava		
FINISH	— — —		N:A	1/1

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SECTION A-A
SCALE 2:1



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X:±0.30	.X':±5°	PART NO. A05FC-SNFCC-H20	TITLE: 0.5mm间距卧贴翻盖式下接H2.0高		
.XX:±0.20	.XX':±3°				
.XXX:±0.05	.XXX':±1°				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1