





SPECIFICATIONS

Current Rating: 1.5 Amps  
Insulation Resistance: 1000M  $\Omega$  Min  
Contact Resistance: 20m  $\Omega$  Max  
Withstanding Voltage: AC 500V  
Operation Temperature: -40° to +105°  
Contact Material: Brass  
Standard: PA6T  
Insulator Material: Polyester (UL 94V-0)  
Contact Plating: Gold Flash  
Max. Processing Temp: 240° C for 30-60 seconds  
(260° C for 5 seconds)



RECOMMEND P. C. B LAYOUT  
PCB TOLERANCE:  $\pm 0.05$  (TOP VIEW)



深圳市韩下电子有限公司

|                                                                                                                                                                 |    |                                |          |       |            |                          |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|----|--------------------------------|----------|-------|------------|--------------------------|
| UNLESS OTHERWISE SPECIFIED TOLERANCE<br>X : $\pm 0.30$ X° : $\pm 5^\circ$<br>X.X : $\pm 0.25$ X.X° : $\pm 1^\circ$<br>X.XX : $\pm 0.20$ X.XX° : $\pm 0.5^\circ$ |    | DRAWN NAME: HX PZ2.0-2x9P TP-D |          |       |            |                          |
|                                                                                                                                                                 |    | SIZE                           | A4       | SCALE | N:1        | PROUCT NO.               |
|                                                                                                                                                                 |    | REV                            | A        | UNIT  | mm         | PROJECT                  |
| DRAW;                                                                                                                                                           | 黄彬 | 2022/10/28                     | CHECKED: | 张伟    | 2022/10/28 | APPROVED: 罗小春 2022/10/28 |

| No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 1      | 0.00   | 2.00   | 11     | 20.00  | 22.00  | 21     | 40.00  | 42.00  | 31     | 60.00  | 62.00  |
| 2      | 2.00   | 4.00   | 12     | 22.00  | 24.00  | 22     | 42.00  | 44.00  | 32     | 62.00  | 64.00  |
| 3      | 4.00   | 6.00   | 13     | 24.00  | 26.00  | 23     | 44.00  | 46.00  | 33     | 64.00  | 66.00  |
| 4      | 6.00   | 8.00   | 14     | 26.00  | 28.00  | 24     | 46.00  | 48.00  | 34     | 66.00  | 68.00  |
| 5      | 8.00   | 10.00  | 15     | 28.00  | 30.00  | 25     | 48.00  | 50.00  | 35     | 68.00  | 70.00  |
| 6      | 10.00  | 12.00  | 16     | 30.00  | 32.00  | 26     | 50.00  | 52.00  | 36     | 70.00  | 72.00  |
| 7      | 12.00  | 14.00  | 17     | 32.00  | 34.00  | 27     | 52.00  | 54.00  | 37     | 72.00  | 74.00  |
| 8      | 14.00  | 16.00  | 18     | 34.00  | 36.00  | 28     | 54.00  | 56.00  | 38     | 74.00  | 76.00  |
| 9      | 16.00  | 18.00  | 19     | 36.00  | 38.00  | 29     | 56.00  | 58.00  | 39     | 76.00  | 78.00  |
| 10     | 18.00  | 20.00  | 20     | 38.00  | 40.00  | 30     | 58.00  | 60.00  | 40     | 78.00  | 80.00  |