



Part Number : [797581010](#)

Product Description : Pre-Crimped Lead Pico-EZmate Female-to-Pico-EZmate Female, Gold (Au) Plating, 300.00mm Length, 28 AWG, White

Series Number : 79758

Status : Active

Product Category : Power and Signal Cable Assemblies



---

## Documents & Resources

### Drawings

[797581010\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Power and Signal Cable Assemblies
Series	79758
Description	Pre-Crimped Lead Pico-EZmate Female-to-Pico-EZmate Female, Gold (Au) Plating, 300.00mm Length, 28 AWG, White
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Pico-EZmate Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	Pico-EZmate
UPC	889056818605

### Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	White
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.450/g
Packaging Type	Bag
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1516
Wire Size (AWG)	28

---

### Use with Part(s)

Description	Part Number
Pico-EZmate Receptacle Housings and Terminals	<u>78172</u>

---

---

This document was generated on Jan 21, 2025