




标识点
Identification points



焊接顺序点
Weld sequence points



防护等级 (Ingress protection) IP50(头座插合时When the headstand is plugged in)

插拔测试 (Plugging and unplugging test)	<5000次
-------------------------------------	--------

产品耐温 (The product is temperature resistant) -55°C / $+150^{\circ}\text{C}$

盐雾腐蚀 (Salt Spray Corrosion) >72 hr

测试电压 (kV rms) 针芯-针芯	1.45
---------------------	------

测试电压 (kV rms) 针芯-外壳	1.3
---------------------	-----

额定电流Current rating	8A
--------------------	----

导体接触规格 Conductor contact specifications	0.9
---	-----

最大接触电阻(mΩ)	Maximum Contact Resistance (mΩ)	5.0
------------	---------------------------------	-----

绝缘电阻(Insulation resistance)	5000MΩ (常态)
-----------------------------	-------------

屏蔽 (分钟) Shielding (min) 100 g (6 ms)


外壳材料 Housing material	金属件铜合金镀镍镀铬 (Metal parts: copper alloy nickel plated and chrome plated)
-----------------------	---

导体材料 Conductor material 铜合金镀金 (Copper alloy gold-plated)

绝缘体材料 Insulator material PPS (可选PEEK) PPS (optional PEEK)

固定类型 Fixed type 电缆夹头 (Cable chucks)

护套电缆外径 (mm)	8.3-9.2mm
Sheath cable outer diameter (mm)	



1: 连接器组装生产所有公差通常为0.1mm,2: 插座直接拧入螺孔中, 螺纹 +0.05mm
1: All tolerances are usually 0.1mm for connector assembly production, 2: The socket is
screwed directly into the threaded hole, the thread is +0.05mm

TINGRILIGUN

东莞市通瑞电子科技有限公司
TongRuiJoin
guan Tongrui Electronic Technology Co., Ltd
www.Cltfre.com

单芯图纸Single-core drawings

单位unit:mm	修改revise:A0
-----------	-------------

视图view:

型号Model	BB EGG 2B 10 CSAD927
---------	----------------------

2B系列直插头2B Series Straight Plug