

标识点
 Identification points

焊接顺序点
 Weld sequence points

防护等级 (Ingress protection)	IP50(头座插合时When the headstand is plugged in)
插拔测试 (Plugging and unplugging test)	<5000次
产品耐温 (The product is temperature resistant)	-55° C / +150° C
盐雾腐蚀 (Salt Spray Corrosion)	>72 hr
测试电压 (kV rms) 针芯-针芯	1.5
测试电压 (kV rms) 针芯-外壳	1.25
额定电流Current rating	10A
导体接触规格 Conductor contact specifications	0.9
最大接触电阻(mΩ)Maximum Contact Resistance (mΩ)	5.0
绝缘电阻(Insulation resistance)	5000MΩ (常态)
屏蔽 (分钟) Shielding (min)	100 g (6 ms)

外壳材料	Housing material	金属件铜合金镀镍镀铬 (Metal parts: copper alloy nickel plated and chrome plated)
导体材料	Conductor material	铜合金镀金 (Copper alloy gold-plated)
绝缘体材料	Insulator material	PPS (可选PEEK) PPS (optional PEEK)

固定类型 Fixed type	电缆夹头 (Cable chucks)
护套电缆外径 (mm) Sheath cable outer diameter (mm)	8.3-9.2mm

