

Specifications:

规格:

Voltage rating:50V AC/DC

额定电压: 50V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-25°C-+85°C



温度范围: -25°C ~ $+85^{\circ}\text{C}$

Insulation resistance:100MΩ min

绝缘电阻: 100MΩ Min


Contact resistance: 50mΩ Max

接触电阻: 50mΩ Max



X1254 W V S - 2xXX A - LP XX
 (1) (2) (3) (4) (5) (6) (7) (8)

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:2xXX-2x05~2x20 Pin
- 6.Type:A-Double-row connector
- 7.Material:LP-LCP UL94V-0 ;
- 8.Plating:XX-V01:Gold Plated ; SN:Tin Plated



Recommended P.C.B Layout
General Tolerance ± 0.05

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
2x05	5.00	9.50	8.70	2x13	15.00	19.50	18.70
2x06	6.25	10.75	9.95	2x14	16.25	20.75	19.95
2x07	7.50	12.00	11.20	2x15	17.50	22.00	21.10
2x08	8.75	13.25	12.45	2x16	18.75	23.25	22.45
2x09	10.00	14.50	13.70	2x17	20.00	24.50	23.70
2x10	11.25	15.75	14.95	2x18	21.25	25.75	24.95
2x11	12.50	17.00	16.20	2x19	22.50	27.00	26.20
2x12	13.75	18.25	17.45	2x20	23.75	28.25	27.45

X1254WVS-2xXXA-LPXX	LCP	Phosphor	X1254H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector
DWN		VIEW: 	PART NO.: X1254WVS-2xXXA-LPX
CHKD		UNIT: mm/in	DWG NO.: X-X1254WVS-2xXXA-LPXX
APPD		SIZE: A4	

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED