



发行版本 Revision	修改内容 Description	制图 Drawing	日期 Date
A / 0	First release	Ding	2023.06.02



Pin Assignment Front View	
3Pin	4Pin



- NOTES:
- Rated voltage/current : 3pin: 60V/3A
4pin: 60V/3A
 - Wire Range :
3pin: 24-22AWG/0.25~0.34mm²
4pin: 24-22AWG/0.25~0.34mm²
 - Cable Range: OD03.5~05.5mm
 - Wire connection mode: Screw
 - Operating temperature: -40℃ ~+85℃
 - RoHS Compliance

8	Hex key	Carbon Steel	1	PCS
7	Pressure Screw	PA66 UL94-V0	1	PCS
6	Pinch ring	PA66 UL94-V0	1	PCS
5	Seal	NBR, Black	1	PCS
4	Body	PA66 UL94-V0	1	PCS
3	Contact	Brass with gold plated	3-4	PCS
2	Insert	PA66 UL94-V0	1	PCS
1	Screw	Brass with nickel plated	1	PCS
编号 No.	品名 Part Name	描述 Description	单位 Unit	用量 Qty

dosinconn DOSIN INDUSTRIAL(HK)CO.,LTD 江门市德索连接器有限公司 Jiangmen Dosin Connector Co., LTD Web: http://www.dosinconn.com Dosin2005@dosin-china.com Tel: (0086)769-8115 3906 Fax: (0086)769-81875836											
客户料号 Cus' P/N		图 号 File No.		RHT-634-3368		品 名 Name		M8 Male connector Assembly, Screw joint			
未注公差 Unless Otherwise Specified			单 位 Unit	mm	版 本 Revision	A/0		图纸确认 APPROVAL		日期 Date	
线性 Linear	0.5~6		±0.1			Third Angle Projection		绘 图 Drawing		Ding	2023.06.02
	>6~30		±0.2					审 核 Checked		Jim	2023.06.02
	>30		±2%								
角度 Angles			±3°				客户确认 Customer Approved				