






Specifications:
Rating Voltage : 300V AC. DC
Rating Current : 7A AC. DC
Contact Rsdistanuce: 20mΩ Max
Insulation Reisenhower: 1000MΩ Min
Withstanding Voltage: 1500V AC/minute
Temperature range: -25℃~85℃
Materials: Nylon UL94V-0(2)

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL42001(SL)-Y	TITLE: 4.2mm Pitch Housing
.XX: ± 0.15	.X° : ± 2.0°	DR: Chen Quan Long	DATE:21/08/01
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:21/08/01
FINISH: _____		APPD:Ren An De	DATE:21/08/01
DRAWING NO:		UNITS: mm	PAGE: 1/1
		REV. : A	



Specifications:
Rating Voltage : 300V AC. DC
Rating Current : 7A AC. DC
Contact Rsdistance: 20mΩ Max
Insulation Reisenhower: 1000MΩ Min
Withstanding Voltage: 1500V AC/minute
Temperature range: -25℃~85℃
Materials: Nylon UL94V-0(2)


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL42001 (SL) -R		TITLE: 4.2mm Pitch Housing	
.XX: ± 0.15	.X° : ± 2.0°			PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	DR: Chen Quan Long	DATE:21/08/01	SCALE: N/A	
FINISH: _____		CHKD: Wu Hui	DATE:21/08/01	PAGE: 1/1	
DRAWING NO: _____		APPD:Ren An De	DATE:21/08/01	UNITS: mm	REV. : A



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:
Rated voltage: 300V AC.DC
Rated current: 7A AC DC
Contact resistance: $\leq 20 \text{ m}\Omega$
Insulation resistance: $\geq 1000 \text{ M}\Omega$
Withstand voltage: 1500V AC/minute
Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
Wire range: AWG#26~#18
Materials:
Terminal: Phosphor bronze, Tin plated

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
. X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DL42001 (SL)-T		TITLE: 4.20 mm Pitch Crimp Terminal	
. XX: ± 0.15	. X° : $\pm 2.0^{\circ}$				
. XXX: ± 0.01	. XX° : $\pm 1.0^{\circ}$	DR:Chen Quan Long	DATE:23/02/11	PART NO:	
FINISH:		CHKD: Wu Hui	DATE:23/02/11		
DRAWING NO:		APPD:Ren An De	DATE:23/02/11	SCALE: N/A	PAGE: 1/1
				UNITS: mm	REV.: A



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:
Rated voltage: 300V AC.DC
Rated current: 7A AC DC
Contact resistance: $\leq 20 \text{ m}\Omega$
Insulation resistance: $\geq 1000 \text{ M}\Omega$
Withstand voltage: 1500V AC/minute
Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
Wire range: AWG#28~#16
Materials:
Terminal: Phosphor bronze, Tin plated

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD	
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DL42001 (SL)-RT	TITLE: 4.20 mm Pitch Crimp Terminal
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$		
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	DR:Chen Quan Long	DATE:23/02/11
FINISH:		CHKD: Wu Hui	DATE:23/02/11
DRAWING NO:		APPD:Ren An De	DATE:23/02/11
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A