

RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.05.24

SPECIFICATIONS

- Current rating: 1A
- Temperature range: -40°C ~ +105°C
- Insulation resistance: 1000MΩ Min.
- Withstanding voltage: 500V AC/ minute.
- Contact resistance: 30mΩ Max.

Material:

Insulator Material:PA6T (UL 94V-0) Black

Contact Material:Brass

Plating:Matte Tin or gold plated over Nickel





Ordering Code:

BH127VS-XXP-H49

1 2

1.序列号

2.Pin位数: 2x03=06P



P.C.B Hole Layout

X.±0.50	X.°±	PART NO: BH127VS-XXP-H49		XFCN 兴飞连接器							
.X±0.25	.X°±										
.XX±0.15	.XX°±	TITLE: 1.27mm Box Header Connectors		0769-82001899							
.XXX±0.10	.XXX°±			www.xfconn.com							
UNITS:	mm	DWG NO: /									
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN											
							APPD	Chen ZhiQiang			
							CHKD	Liu Wei	VIEW		
							DRAW	Chen HongJiang	SCALE	SHEET	REV
		DATE	2024.11.22	NONE	1/1	A1					