








REV.	REVISION DESCRIPTION	DATE	APPD

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL42009-2R		TITLE: 4.2mm Pitch Wire To Wire Receptacle Housing	
.XX: ± 0.2	.X° : ± 2.0°			PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:2021.11.27	SCALE: N/A	
FINISH:		CHKD:Wu Hui	DATE:2021.11.27	PAGE: 1/1	
DRAWING NO:		APPD:Ren An De	DATE:2021.11.27	UNITS: mm	REV.: A



SECTION A-A



SECTION B-B

NOTES:

Rated voltage: 300V AC/DC

Rated current: 9A AC/DC

Contact resistance: $\leq 20 \text{ m}\Omega$

Insulation resistance: $\geq 1000 \text{ M}\Omega$

Withstand voltage: 1500V AC/minute

Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$

Wire range: AWG#28~#20

Materials:

Terminal: Phosphor bronze, Tin plated

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DL42009-RT		TITLE: 4.2mm Pitch Wire To Wire Crimp Terminal	
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$			PART NO:	
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	DR: Chen Quan Long	DATE: 2020.10.23	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE: 2020.10.23	PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE: 2020.10.23	UNITS: mm	REV.: A