





REV.	REVISION DESCRIPTION	DATE	APPD

- NORES:**
- 1. Rated voltage: 250V AC.DC
 - 2. Rated current: 5A AC DC
 - 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000 \text{ m}\Omega$
 - 5. Withstand voltage: 1500V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$
 - 7. Materials: Nylon UL94V-0 (2)
 - 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DL37001 (5500)-Y	TITLE: 3.70 mm Pitch Wire To Wire Housing
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$		
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	DR: Chen Quan Long	DATE: 19/08/01
FINISH:		CHKD: Wu Hui	DATE: 19/08/01
DRAWING NO:		APPD: Ren An De	DATE: 19/08/01
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A




REV.	REVISION DESCRIPTION	DATE	APPD

- NORES:**
- 1. Rated voltage: 250V AC.DC
 - 2. Rated current: 5A AC DC
 - 3. Contact resistance: ≤20 mΩ
 - 4. Insulation resistance: ≥1000 mΩ
 - 5. Withstand voltage: 1500V AC/minute
 - 6. Ambient temprature: -40℃~105℃
 - 7. Materials: Nylon UL94V-0(2)
 - 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL37001 (5600)-R	TITLE: 3.70 mm Pitch Wire To Wire Housing
.XX: ± 0.15	.X° : ± 2.0°	DR: Chen Quan Long	DATE: 19/08/01
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE: 19/08/01
FINISH:		APPD: Ren An De	DATE: 19/08/01
DRAWING NO:		UNITS: mm	PAGE: 1/1
			REV.: A

REV.	REVISION DESCRIPTION	DATE	APPD



NOTES:

Rated voltage: 250V AC.DC

Rated current: 5A AC DC

Contact resistance: $\leq 20 \text{ m}\Omega$

Insulation resistance: $\geq 1000 \text{ M}\Omega$



Withstand voltage: 1500V AC/minute

Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$


Wire range: AWG#22~#18

Materials:

Terminal: Phosphor bronze, Tin plated




SECTION A-A





SECTION B-B

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DL37001 (5500)-T	TITLE: 3.70 mm Pitch Crimp Terminal
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR:Chen Quan Long	DATE:19/08/01
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE:19/08/01
FINISH:		APPD:Ren An De	DATE:19/08/01
DRAWING NO:		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A


REV.	REVISION DESCRIPTION	DATE	APPD



NOTES:
 Rated voltage: 250V AC.DC
 Rated current: 5A AC DC
 Contact resistance: ≤20 mΩ
 Insulation resistance: ≥1000 MΩ
 Withstand voltage: 1500V AC/minute
 Ambient temprature:-40℃~+105℃
 Wire range: AWG#28~#20
 Materials:
 Terminal: Phosphor bronze,Tin plated



SECTION A-A



SECTION B-B

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL37001 (5600) -RT	TITLE: 3.70 mm Pitch Crimp Terminal
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:19/08/01
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:19/08/01
FINISH:		APPD:Ren An De	DATE:19/08/01
DRAWING NO:		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A