



NOTES:

1. Rated voltage/current : 3pin: 60V/3A
4pin: 60V/3A

2. Wire Range :

3pin: 24-22AWG/0.25~0.34mm²

4pin: 24-22AWG/0.25~0.34mm²

3. Cable Range: 0D03.5~05.5mm

4. Wire connection mode: Screw
5. Operating temperature: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$

6. RoHS Compliance

9	Hex key	Carbon Steel	1	PCS
8	Pressure Screw	PA66 UL94-V0	1	PCS
7	Pinch ring	PA66 UL94-V0	1	PCS
6	Seal	NBR, Black	1	PCS
5	Body	PA66 UL94-V0	1	PCS
4	Contact	Brass with gold plated	3-4	PCS
3	Insert	PA66 UL94-V0	1	PCS
2	Screw	Brass with nickel plated	1	PCS
1	O-ring	NBR, Black	1	PCS
编号 No.	品名 Part Name	描 述 Description	单位 Unit	用量 Qty

 DOSIN INDUSTRIAL(HK)CO.,LTD 江门市德索连接器有限公司 Jiangmen Dosin Connector Co., LTD				Web: http://www.dosinconn.com Dosin 2005@dosin-china.com Tel: (0086)769-8115 3906 Fax: (0086)769-81875836					
客户料号 Cus' P/N		图号 File No.		RHT-634-3369		品名 Name		M8 Female connector Assembly, Screw joint	
未注公差 Unless Otherwise Specified		单位 Unit	mm	版本 Revision	A/0	图纸确认 APPROVAL		日期 Date	
线性 Linear	0.5~6	±0.1	比例 Scale	—	 Third Angle Projection	绘图 Drawing	Ding	2023.06.02	
	>6~30	±0.2				审核 Checked	Jim	2023.06.02	
	>30	±2%				页码 Page	1/1	客户确认 Customer Approved	
角度 Angles		±3°							