






REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
1. Rated voltage: 250V AC. DC
 2. Rated current: 7A AC DC
 3. Contact resistance: $\leq 20\text{ m}\Omega$
 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 5. Withstand voltage: 1500V AC/minute
 6. Ambient temprature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
 7. Material : Nylon UL94V-0(2)
 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME:	TITLE: 5.08 mm Pitch Wire To Wire Housing
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$	DR:Chen Quan Long	DATE:20/12/30
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	DATE:20/12/30	PART NO:
FINISH:		CHKD: Wu Hui	DATE:20/12/30
DRAWING NO:	APPD:Ren An De	DATE:20/12/30	SCALE: N/A
			PAGE: 1/1
			UNITS: mm
			REV.: A






REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:
Rated voltage: 250V AC.DC
Rated current: 7A AC DC
Contact resistance: ≤20 mΩ
Insulation resistance: ≥1000 MΩ
Withstand voltage: 1500V AC/minute
Ambient temprature:-40℃~+105℃
Wire range: AWG#18~#24
Materials:
Terminal: Phosphor bronze,Tin plated

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL50802(TJC10)-T-01	TITLE: 5.08 mm Pitch Wire To Wire Terminal
.XX: ± 0.15	.X° : ± 2.0°	DR:Yuan Jun Jong	DATE:20/12/30
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:20/12/30
FINISH: _____		APPD:Ren An De	DATE:20/12/30
DRAWING NO:		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:
Rated voltage: 250V AC.DC
Rated current: 7A AC DC
Contact resistance: $\leq 20\text{ m}\Omega$
Insulation resistance: $\geq 1000\text{ M}\Omega$
Withstand voltage: 1500V AC/minute
Ambient temprature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
Wire range: AWG#18~#24
Materials:
Terminal: Phosphor bronze,Tin plated

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DL50802(TJC10)-RT-01		TITLE: 5.08 mm Pitch Wire To Wire Terminal	
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$				
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	DR:Yuan Jun Jong	DATE:20/12/30	PART NO:	
FINISH: _____		CHKD: Wu Hui	DATE:20/12/30	SCALE: N/A	PAGE: 1/1
DRAWING NO:		APPD:Ren An De	DATE:20/12/30	UNITS: mm	REV.: A